



Instrucțiuni de asamblare




3015

RoHS  ISO9001:2000

Instrument necesar



Creion




Șurubelniță




burghiu



Nivel de spirit




ciocan de cauciuc




silicon


Părți




Tray




Glass




Glass




Glass



Glass




Screw



Screw




Expand tube




Wall profile




PJ-4026




CT-8DST90




PJ-4419




PJ-4303



CT-8DSTC




CT-8BMX90




PJ-4418




PJ-4007



LS-1009




PJ-4543




LZ-5012




PJ-4561




PJ-4509




Side cover




PJ-4012




Aluminum
bottom bar



PJ-4514/
PJ-4515






PJ-4416




LG-2004






PJ-4317



Dimensiui cabina	L1
1000X800	952
1000X900	952
1200X800	1152
1200X900	1152







Vă rugăm să introduceți cu atenție elementele laterale în profilele de perete, lăsați protectorul de margine pe sticlă



